

Accessoires

Bodycam System



zepcam™

PROFESSIONAL BODYCAM SOLUTIONS










Image	Code	Name & Availability	Description
	T2-M04	Magnet Mount Available for ZEPCAM T2+ and ZEPCAM T3Live	Magnet Mount Kit for garment mounting available for metric or imperial magnets (magnets not supplied) Magnet Mount Kit to fit metric magnets sized 20mm x 5mm. Unassembled and no magnets included. Includes 1 x front part with dock, 1 x rear part, 8 x caps and 8 washers. Also includes instructions sheet (shown below). Connects to bodycam using the T2- M02 (Fixed stud) or T2-M03 (Tilt stud). Includes safety cord for attachment to jacket.
	T2-M03	Tilt stud for T2 bodycam Available for ZEPCAM T2+	Tilt stud for T2+ series bodycams. Makes adjustment of mount possible. Necessary to connect to T2 mounts
	T2-M09	Molle System Mount Available for ZEPCAM T2+ and ZEPCAM T3Live	Allows secure and easy attachment to any MOLLE loop system using webbing straps and two press-studs.
	T2-M08	Epaulette mount for T2+ series Available for ZEPCAM T2+ and ZEPCAM T3Live	Epaulette mount for T2+ series bodycams. Connects to bodycam using the T2-M02 Shoulder mount (Fixed stud) or T2-M03 (Tilt stud).
	T2-M14	Dock tag mount Available for ZEPCAM T2+ and ZEPCAM T3Live	Single-Tongued Tag Mounting Dock with 41mm Tongue Width Fits onto existing shirt or clothing loops measuring 41mm or over in width.
	T2-M07	Center Chest harness Available for ZEPCAM T2+ and ZEPCAM T3Live	Adjustable 4 point-harness for T2+ series bodycams. Connects to bodycam using the T2-M02 (Fixed stud) or T2-M03 (Tilt stud).
	T2-M11	Shoulder harness Available for ZEPCAM T2+ and ZEPCAM T3Live	Adjustable 3 point-harness for T2+ series bodycams. Connects to bodycam using the T2-M02 (Fixed

Image	Code	Name & Availability	Description
	T2-M06	Clamp mount for T2+ series Available for ZEPCAM T2+ and ZEPCAM T3Live	Clamp mount for T2+ series bodycams, designed for extra stability. Connects to bodycam using the T2-M02 (Fixed stud) or T2-M03 (Tilt stud).
	T2-M02	Fixed stud Available for ZEPCAM T2+	Fixed stud for T2+ series bodycams. Fixed mount position. Necessary to connect to
	T2-M05	Garment mount Available for ZEPCAM T2+	<ul style="list-style-type: none"> • 'Screw-to-Fit' dock allows T2+ series bodycams to be mounted on garments. • Connects to bodycam using the T2-M02 (Fixed stud) or T2-M03 (Tilt stud).
	RAM-B-238	Car Mount Available for ZEPCAM T2+	RAM V-Base Strap Clamp 1 Ball Arm RAM-B-238 Diamond Adaptor Mount.
	T2-M17	T2-M17 Available for ZEPCAM T2+ and ZEPCAM T3Live	Fully adjustable to suit all handlebars from 20 - 30mm diameter. Supplied with rubber protection sleeve to cushion your equipment from vibrations and protect your handlebars.
	Omnikey 5427CK	RFID Reader	At the docking station users can identify themselves using a RFID smartcard. Currently supported RFID reader is Omnikey 5427 and supported protocols include iCLASS Seos®, HID Prox®, iCLASS SE®, MIFARE Classic® and MIFARE® DESFire® EV1, NFC.
		Ewent numeric keypad	Numeric keypad used to login with a dynamic user ID.